



FlexScape Inground IL9

Inground, Composite, Zoomable Optics, FlexScape, Bronze, 3000K, 12V

Inground, Composite, Zoomable Optics, FlexScape, Bronze, 3000K, 12V - 100 lm/W

Hadco FlexScape LED inground luminaire IL9 opens new horizons for low-voltage landscape lighting. It is designed for optimal LED performance and superior flexibility. The luminaire creates visual interest for pathways, walls, columns and foliage. Its rugged housing installs directly into the soil. In addition to low-energy outdoor lighting, it features convenient on-site beam adjustability. This allweather luminaire comes with 100% molded silicone gaskets.

Product data

General information	
Lamp Source Code	LED
Lamp Watts	11
Number of Lamps	1
Colour Temperature	3000 K
CRI	70
Photometric Distribution Type	General Diffuse
Mounting	In Ground
Number Of Pieces	1

Operating and electrical	
Voltages	12 V
Luminaire Input Watts	11

Conduit Connection	7/8 inch knockout
--------------------	-------------------

Mechanical and housing	
Enclosure	Metal and Plastic

Initial performance (IEC compliant)	
Luminaire Lumens	700
Efficacy	100 lm/W

Product data	
Order product name	FLEXSCAPE,INGROUND,WW,BLK
EAN/UPC - Product	783352021588
Order code	IL9DW-A

FlexScape Inground IL9

Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	912401150005
Net Weight (Piece)	0.001 kg
Catalog Number	IL9DW-A

Catalog Number Description	Inground, Composite, Zoomable Optics, FlexScape, Bronze, 3000K, 12V
-----------------------------------	---

