



Wal-Lyter LED Recessed Wall Wash

LED Recessed Wall Wash, 2'

LED Recessed Wall Wash, 2'

The Day-Brite / CFI Wal-Lyter LED Recessed Wallwash is a high performance luminaire that delivers good light levels and an even wash of light. Low-iridescent semi-specular reflectors do not protrude below the ceiling line. This provides a clean appearance while controlling the light output of high efficiency LED boards to illuminate vertical surfaces uniformly.

Product data

General Information	
Lamp Source Code	LED
Colour Temperature	3500K
CRI	80
Photometric Distribution Type	Direct
Mounting	Recessed T-Bar / T-Grid
Operating and Electrical	
Voltages	120/277/UNIV V
Luminaire Input Watts	32
Mechanical and Housing	
Fixture Size	1 ft x 2 ft
Shape	Rectangular

Initial Performance (IEC Compliant)	
Luminaire Lumens	1736
Product Data	
Order product name	WLRN17L835-2-UNV
EAN/UPC - Product	781370207007
Order code	WLRN17L835-2-UNV
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	912401260250
Net Weight (Piece)	0.001 kg
Catalog Number	WLRN17L835-2-UNV
Catalog Number Description	LED Recessed Wall Wash, 2'