



# Arioso Recessed LED

## 2x2, 3800 Nominal Delivered Lumens, 3500K, Frosted Acrylic Lens

2x2, 3800 Nominal Delivered Lumens, 3500K, Frosted Acrylic Lens - 95 lm/W

The Day-Brite / CFI Arioso Recessed LED offers standard-setting efficiency without aesthetic compromise. These LED luminaires combine state-of-the-art, flexible and globally- recognized LED lighting platforms with proven Arioso optical combinations.

### Product data

<b>General information</b>		<b>Efficacy</b>	
Lamp Source Code	LED	95 lm/W	
Colour Temperature	3500 K	<b>Product data</b>	
CRI	80	Order product name	2AVEG38L835-2-ACR-UNV
Photometric Distribution Type	Direct	EAN/UPC - Product	781370296926
Mounting	Recessed T-Bar / T-Grid	Order code	2AVEG38L835-2-ACR-UNV
<b>Operating and electrical</b>		Numerator - Quantity Per Pack	1
Voltages	UNIV V	Numerator - Packs per outer box	1
Luminaire Input Watts	40	Material Nr. (12NC)	912401260941
<b>Mechanical and housing</b>		Net Weight (Piece)	5.500 kg
Fixture Size	2 ft x 2 ft	Catalog Number	2AVEG38L835-2-ACR-UNV
Shape	Square	Catalog Number Description	2x2, 3800 Nominal Delivered Lumens, 3500K, Frosted Acrylic Lens
<b>Initial performance (IEC compliant)</b>			
Luminaire Lumens	3800		