



# DuaLED Recessed

1DLG36L835-4-D-UNV

1x4, 3600 Nominal Delivered Lumens, 3500K, Diffuse - 95 lm/W

DuaLED was thoughtfully developed as a sustainable luminaire with a modern appearance and uncomplicated design, also offering exceptional quality and performance, for an outstanding benefit to the customer. DuaLED is a highly efficient, architecturally styled recessed LED luminaire designed with a minimalistic strategy to achieve sustainable objectives. It combines an extremely low profile with clean aesthetics and is powered by highly efficient advanced LED sources, providing the utmost in comfortable efficient lighting. Driver and integral control options ensure optimization for every application. Designed for excellent visual comfort, DuaLED is perfect for a wide variety of general applications like offices, schools, retail, or healthcare.

## Product data

General Information	
Lamp Source Code	LED
Color Temperature	3500K
CRI	80
Photometric Distribution Type	Direct
Mounting	Recessed
Operating and Electrical	
Voltages	120/277/347 V
Luminaire Input Watts	38
Mechanical and Housing	
Fixture Size	1 ft x 4 ft
Shape	Rectangular

Initial Performance (IEC Compliant)	
Luminaire Lumens	3600
Efficacy	95 lm/W
Product Data	
Order product name	1DLG36L835-4-D-UNV
EAN/UPC - Product	782343649145
Order code	912401261294
Local order code	4364914
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	912401261294
Net Weight (Piece)	0.001 kg
Commercial Code	1DLG36L835-4-D-UNV-DIM
Catalog Number Description	1x4, 3600 Nominal Delivered Lumens, 3500K, Diffuse
Quick Ship	-

