



# DuaLED Recessed

**1x4, 4700 Nominal Delivered Lumens, 3500K, Diffuse**

1x4, 4700 Nominal Delivered Lumens, 3500K, Diffuse – 90 lm/W

DuaLED was thoughtfully developed as a sustainable luminaire with a modern appearance and uncomplicated design, also offering exceptional quality and performance, for an outstanding benefit to the customer. DuaLED is a highly efficient, architecturally styled recessed LED luminaire designed with a minimalistic strategy to achieve sustainable objectives. It combines an extremely low profile with clean aesthetics and is powered by highly efficient advanced LED sources, providing the utmost in comfortable efficient lighting. Driver and integral control options ensure optimization for every application. Designed for excellent visual comfort, DuaLED is perfect for a wide variety of general applications like offices, schools, retail, or healthcare.

## Product data

<b>General Information</b>		<b>Shape</b>	
Lamp Source Code	LED	Rectangular	
Colour Temperature	3500K	<b>Initial Performance (IEC Compliant)</b>	
CRI	80	Luminaire Lumens	4700
Photometric Distribution Type	Direct	Efficacy	90 lm/W
Mounting	Recessed	<b>Product Data</b>	
<b>Operating and Electrical</b>		Order product name	1DLG47L835-4-D-UNV
Voltages	120/277/347 V	EAN/UPC - Product	782343040768
Luminaire Input Watts	52	Order code	1DLG47L835-4-D-UNV-DIM
<b>Mechanical and Housing</b>		Numerator - Quantity Per Pack	1
Fixture Size	1 ft x 4 ft	Numerator - Packs per outer box	1
		Material Nr. (12NC)	912401267328

## DuaLED Recessed

Net Weight (Piece)	0.001 kg
Catalog Number	1DLG47L835-4-D-UNV-DIM
Catalog Number Description	1x4, 4700 Nominal Delivered Lumens, 3500K, Diffuse

