



# SofTrace Surface LED

**2x2, Surface, 3000 Nominal Delivered Lumens, 80 CRI, 3500K, Diffuse-Ribbed**

2x2, Surface, 3000 Nominal Delivered Lumens, 80 CRI, 3500K, Diffuse-Ribbed

SofTrace Surface LED brings new meaning to the concept of combining style with performance. Equipped with a fresh streamlined design and innovative technology, SofTrace provides a huge step forward for the lighting industry. The sleek profile design belies the true “horsepower under the hood”. With efficiency levels exceeding 95% and lumens per Watt as great as 87, an architectural product now delivers leading edge performance for the most environmentally conscious user.

## Product data

| General Information                 |               |
|-------------------------------------|---------------|
| Lamp Source Code                    | LED           |
| Colour Temperature                  | 3500K         |
| CRI                                 | 80            |
| Photometric Distribution Type       | Direct        |
| Mounting                            | Surface       |
| Operating and Electrical            |               |
| Voltages                            | 120/277/347 V |
| Luminaire Input Watts               | 33            |
| Mechanical and Housing              |               |
| Fixture Size                        | 2 ft x 2 ft   |
| Shape                               | Square        |
| Initial Performance (IEC Compliant) |               |
| Luminaire Lumens                    | 3000          |

| Product Data                    |  |
|---------------------------------|--|
| Order product name              | 2SST30L835-2-D-UNV   |
| EAN/UPC - Product               | 784197044664   |
| Order code                      | 2SST30L835-2-D-UNV-DIM   |
| Numerator - Quantity Per Pack   | 1  |
| Numerator - Packs per outer box | 1  |
| Material Nr. (12NC)             | 912401271486   |
| Net Weight (Piece)              | 0.001 kg   |
| Catalog Number                  | 2SST30L835-2-D-UNV-DIM   |
| Catalog Number Description      | 2x2, Surface, 3000 Nominal Delivered Lumens, 80 CRI, 3500K, Diffuse-Ribbed |

## SofTrace Surface LED

