



APX LED High Bay

APX08LL40-UNV

8,000 Nominal Delivered Lumens, 4000K, 80 CRI, Narrow Distribution - 129 lm/W

The APX LED High Bay provides durability and high performance for your customer's demanding environments. The APX can be specified for many areas requiring a sealed luminaire, such as laboratories, food processing, parking areas, and other industrial applications. The rugged housing and clear or frosted lens options combine for durable and effective lighting that is also comfortable for the occupants. LED technology provides efficiency, long life, and reduces energy costs.

Product data

| General Information | |
|-------------------------------------|--------------------------------|
| Lamp Source Code | LED |
| Color Temperature | 4000K |
| CRI | 80 |
| Photometric Distribution Type | Direct |
| Mounting | Suspended |
| Operating and Electrical | |
| Voltages | 120/208/240/277/347/480/UNIV V |
| Luminaire Input Watts | 76 |
| Mechanical and Housing | |
| Fixture Size | 48 in |
| Initial Performance (IEC Compliant) | |
| Luminaire Lumens | 8000 |
| Efficacy | 129 lm/W |

| Product Data | |
|---------------------------------|--|
| Order product name | APX08LL40-UNV |
| EAN/UPC - Product | 784197056377 |
| Order code | 912401272291 |
| Local order code | 9705637 |
| Numerator - Quantity Per Pack | 1 |
| Numerator - Packs per outer box | 1 |
| Material Nr. (12NC) | 912401272291 |
| Net Weight (Piece) | 0.001 kg |
| Commercial Code | APX08LL40-UNV-N |
| Catalog Number Description | 8,000 Nominal Delivered Lumens, 4000K, 80 CRI, Narrow Distribution |
| Quick Ship | - |

APX LED High Bay

