



# APX LED High Bay

**24,000 Nominal Delivered Lumens, 4000K, 80 CRI, General Distribution, Frosted Acrylic Lens**

24,000 Nominal Delivered Lumens, 4000K, 80 CRI, General Distribution, Frosted Acrylic Lens - 106 lm/W

The APX LED High Bay provides durability and high performance for your customer's demanding environments. The APX can be specified for many areas requiring a sealed luminaire, such as laboratories, food processing, parking areas, and other industrial applications. The rugged housing and clear or frosted lens options combine for durable and effective lighting that is also comfortable for the occupants. LED technology provides efficiency, long life, and reduces energy costs.

## Product data

|  |                                |                                 |  |
|--|--------------------------------|---------------------------------|--|
| <b>General Information</b>                 |                                | <b>Efficacy</b>                 |  |
| Lamp Source Code                           | LED                            | 106 lm/W                        |  |
| Colour Temperature                         | 4000 K                         | <b>Product Data</b>             |  |
| CRI  | 80                             | Order product name              | APX24LL40-UNV  |
| Photometric Distribution Type              | Direct                         | EAN/UPC - Product               | 784197056575   |
| Mounting                                   | Suspended                      | Order code                      | APX24LL40-UNV-LFA  |
| <b>Operating and Electrical</b>            |                                | Numerator - Quantity Per Pack   | 1  |
| Voltages                                   | 120/208/240/277/347/480/UNIV V | Numerator - Packs per outer box | 1  |
| Luminaire Input Watts                      | 191                            | Material Nr. (12NC)             | 912401272312   |
| <b>Mechanical and Housing</b>              |                                | Net Weight (Piece)              | 0.001 kg   |
| Fixture Size                               | 48 in                          | Catalog Number                  | APX24LL40-UNV-LFA  |
| <b>Initial Performance (IEC Compliant)</b> |                                | Catalog Number Description      | 24,000 Nominal Delivered Lumens, 4000K, 80 CRI, General Distribution, Frosted Acrylic Lens |
| Luminaire Lumens                           | 24000                          |                                 |  |