



# APX LED High Bay

**16,000 Nominal Delivered Lumens, 4000K, 80 CRI, General Distribution, Clear Polycarbonate Lens**

16,000 Nominal Delivered Lumens, 4000K, 80 CRI, General Distribution, Clear Polycarbonate Lens - 126 lm/W

The APX LED High Bay provides durability and high performance for your customer's demanding environments. The APX can be specified for many areas requiring a sealed luminaire, such as laboratories, food processing, parking areas, and other industrial applications. The rugged housing and clear or frosted lens options combine for durable and effective lighting that is also comfortable for the occupants. LED technology provides efficiency, long life, and reduces energy costs.

## Product data

General Information	
Lamp Source Code	LED
Colour Temperature	4000 K
CRI	80
Photometric Distribution Type	Direct
Mounting	Suspended
Operating and Electrical	
Voltages	120/208/240/277/347/480/UNIV V
Luminaire Input Watts	123
Mechanical and Housing	
Fixture Size	48 in

Initial Performance (IEC Compliant)	
Luminaire Lumens	16000
Efficacy	126 lm/W
Product Data	
Order product name	APX16LL40-UNV
EAN/UPC - Product	784197056674
Order code	APX16LL40-UNV-LCP
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	912401272321
Net Weight (Piece)	0.001 kg
Catalog Number	APX16LL40-UNV-LCP
Catalog Number Description	16,000 Nominal Delivered Lumens, 4000K, 80 CRI, General Distribution, Clear Polycarbonate Lens

