



Arioso Recessed LED

2AVEG38L835-2-ACR-347

2x2, 3800 Nominal Delivered Lumens, 3500K, Frosted Acrylic Lens - 95 lm/W

The Philips Day-Brite / Philips CFI Arioso Recessed LED offers standard-setting efficiency without aesthetic compromise. These LED luminaires combine state-of-the-art, flexible and globally- recognized LED lighting platforms with proven Arioso optical combinations.

Product data

General Information	
Lamp Source Code	LED
Color Temperature	3500K
CRI	80
Photometric Distribution Type	Direct
Mounting	Recessed
Operating and Electrical	
Voltages	347 V
Luminaire Input Watts	40
Mechanical and Housing	
Fixture Size	2 ft x 2 ft
Shape	Square
Initial Performance (IEC Compliant)	
Luminaire Lumens	3800

Efficacy	95 lm/W
Product Data	
Order product name	2AVEG38L835-2-ACR-347
EAN/UPC - Product	784197027445
Order code	912401273394
Local order code	9702744
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	912401273394
Net Weight (Piece)	5.447 kg
Commercial Code	2AVEG38L835-2-ACR-347
Catalog Number Description	2x2, 3800 Nominal Delivered Lumens, 3500K, Frosted Acrylic Lens
Quick Ship	-