



APX LED High Bay

12,000 Nominal Delivered Lumens, 4000K, 80 CRI, Wide Distribution, Frosted Polycarbonate Lens

12,000 Nominal Delivered Lumens, 4000K, 80 CRI, Wide Distribution, Frosted Polycarbonate Lens - 119 lm/W

The APX LED High Bay provides durability and high performance for your customer's demanding environments. The APX can be specified for many areas requiring a sealed luminaire, such as laboratories, food processing, parking areas, and other industrial applications. The rugged housing and clear or frosted lens options combine for durable and effective lighting that is also comfortable for the occupants. LED technology provides efficiency, long life, and reduces energy costs.

Product data

General Information		Initial Performance (IEC Compliant)	
Lamp Source Code	LED	Luminaire Lumens	12000
Colour Temperature	4000 K	Efficacy	119 lm/W
CRI	80		
Photometric Distribution Type	Direct	Product Data	
Mounting	Suspended	Order product name	APX12LL40-UNV
		EAN/UPC - Product	784197106973
		Order code	APX12LL40-UNV-W-LFP
		Numerator - Quantity Per Pack	1
		Numerator - Packs per outer box	1
		Material Nr. (12NC)	912401275368
		Net Weight (Piece)	0.001 kg
		Catalog Number	APX12LL40-UNV-W-LFP
		Catalog Number Description	12,000 Nominal Delivered Lumens, 4000K, 80 CRI, Wide Distribution, Frosted Polycarbonate Lens
Operating and Electrical			
Voltages	120/208/240/277/347/480/UNIV V		
Luminaire Input Watts	96		
Mechanical and Housing			
Fixture Size	48 in		

