



# APX LED High Bay

## APX24LL40-UNV

24,000 Nominal Delivered Lumens, 4000K, 80 CRI, Wide Distribution, Frosted Polycarbonate Lens - 116 lm/W

The APX LED High Bay provides durability and high performance for your customer’s demanding environments. The APX can be specified for many areas requiring a sealed luminaire, such as laboratories, food processing, parking areas, and other industrial applications. The rugged housing and clear or frosted lens options combine for durable and effective lighting that is also comfortable for the occupants. LED technology provides efficiency, long life, and reduces energy costs.

### Product data

General Information	
Lamp Source Code	LED
Color Temperature	4000K
CRI	80
Photometric Distribution Type	Direct
Mounting	Suspended
Operating and Electrical	
Voltages	120/208/240/277/347/480/UNIV V
Luminaire Input Watts	191
Mechanical and Housing	
Fixture Size	48 in
Initial Performance (IEC Compliant)	
Luminaire Lumens	24000
Efficacy	116 lm/W

Product Data	
Order product name	APX24LL40-UNV
EAN/UPC - Product	784197158965
Order code	912401278028
Local order code	9715896
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	912401278028
Net Weight (Piece)	0.001 kg
Commercial Code	APX24LL40-UNV-W-LFP
Catalog Number Description	24,000 Nominal Delivered Lumens, 4000K, 80 CRI, Wide Distribution, Frosted Polycarbonate Lens
Quick Ship	-

APX LED High Bay

