



# APX LED High Bay

**24,000 Nominal Delivered Lumens, 4000K, 80 CRI, Wide Distribution, Frosted Polycarbonate Lens**

24,000 Nominal Delivered Lumens, 4000K, 80 CRI, Wide Distribution, Frosted Polycarbonate Lens - 116 lm/W

The APX LED High Bay provides durability and high performance for your customer's demanding environments. The APX can be specified for many areas requiring a sealed luminaire, such as laboratories, food processing, parking areas, and other industrial applications. The rugged housing and clear or frosted lens options combine for durable and effective lighting that is also comfortable for the occupants. LED technology provides efficiency, long life, and reduces energy costs.

## Product data

General Information		Initial Performance (IEC Compliant)	
Lamp Source Code	LED	Luminaire Lumens	24000
Colour Temperature	4000 K	Efficacy	116 lm/W
CRI	80		
Photometric Distribution Type	Direct		
Mounting	Suspended		
Operating and Electrical		Product Data	
Voltages	120/208/240/277/347/480/UNIV V	Order product name	APX24LL40-UNV
Luminaire Input Watts	191	EAN/UPC - Product	784197158965
		Order code	APX24LL40-UNV-W-LFP
		Numerator - Quantity Per Pack	1
		Numerator - Packs per outer box	1
		Material Nr. (12NC)	912401278028
		Net Weight (Piece)	0.001 kg
		Catalog Number	APX24LL40-UNV-W-LFP
		Catalog Number Description	24,000 Nominal Delivered Lumens, 4000K, 80 CRI, Wide Distribution, Frosted Polycarbonate Lens
Mechanical and Housing			
Fixture Size	48 in		

