



LBX LED Linear Suspended

LBX40L840-UNV

4', 4,000 Nominal Delivered Lumens, 4000K, 80 CRI, General Distribution, Flat Diffuse Lens - 128 lm/W

The LBX LED linear suspended luminaires with optional LightBalance Optics provide the versatility required for a wide range of applications. Available in 5 different configurations, LBX is easy to install and can be mounted together in runs. Where precise control is required, LightBalance Optics put the light where it's needed. Choose between narrow, medium, wide, aisle, & double asymmetric distributions.

Product data

General Information	
Colour Temperature	4000K
CRI	80
Photometric Distribution Type	Direct
Mounting	Suspended
Operating and Electrical	
Voltages	347/UNIV V
Luminaire Input Watts	31
Mechanical and Housing	
Fixture Size	48 in
Shape	Linear
Initial Performance (IEC Compliant)	
Luminaire Lumens	4000

Efficacy	128 lm/W
Product Data	
Order product name	LBX40L840-UNV
EAN/UPC - Product	784197184650
Order code	912401278654
Local order code	.
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	912401278654
Net Weight (Piece)	0.001 kg
Commercial Code	LBX40L840-UNV-FD
Catalog Number Description	4', 4,000 Nominal Delivered Lumens, 4000K, 80 CRI, General Distribution, Flat Diffuse Lens
Quick Ship	-

