



LBX LED Linear Suspended

LBX40L840-UNV

4', 4,000 Nominal Delivered Lumens, 4000K, 80 CRI, Medium distribution - 148 lm/W

The LBX LED linear suspended luminaires with optional LightBalance Optics provide the versatility required for a wide range of applications. Available in 5 different configurations, LBX is easy to install and can be mounted together in runs. Where precise control is required, LightBalance Optics put the light where it's needed. Choose between narrow, medium, wide, aisle, & double asymmetric distributions.

Product data

| | | | |
|--|------------|---------------------------------|--|
| General Information | | Efficacy 148 lm/W | |
| Color Temperature | 4000K | | |
| CRI | 80 | | |
| Photometric Distribution Type | Direct | | |
| Mounting | Suspended | | |
| Operating and Electrical | | Product Data | |
| Voltages | 347/UNIV V | Order product name | LBX40L840-UNV |
| Luminaire Input Watts | 31 | EAN/UPC - Product | 784197190965 |
| | | Order code | 912401279083 |
| | | Local order code | 9719096 |
| | | Numerator - Quantity Per Pack | 1 |
| | | Numerator - Packs per outer box | 1 |
| | | Material Nr. (12NC) | 912401279083 |
| | | Net Weight (Piece) | 0.001 kg |
| | | Commercial Code | LBX40L840-UNV-M |
| | | Catalog Number Description | 4', 4,000 Nominal Delivered Lumens, 4000K, 80 CRI, Medium distribution |
| | | Quick Ship | - |
| Initial Performance (IEC Compliant) | | | |
| Luminaire Lumens | 4000 | | |

