



LBX LED Linear Suspended

LBX90L840-UNV

4', 9,000 Nominal Delivered Lumens, 4000K, 80 CRI, General Distribution, Oval Uplight Diffuse Lens - 137 lm/W

The LBX LED linear suspended luminaires with optional LightBalance Optics provide the versatility required for a wide range of applications. Available in 5 different configurations, LBX is easy to install and can be mounted together in runs. Where precise control is required, LightBalance Optics put the light where it's needed. Choose between narrow, medium, wide, aisle, & double asymmetric distributions.

Product data

General Information		Efficacy 137 lm/W	
Color Temperature	4000K		
CRI	80		
Photometric Distribution Type	Direct		
Mounting	Suspended		
Operating and Electrical		Product Data	
Voltages	347/UNIV V	Order product name	LBX90L840-UNV
Luminaire Input Watts	66	EAN/UPC - Product	784197191382
Mechanical and Housing		Order code	912401279118
Fixture Size	48 in	Local order code	9719138
Shape	Linear	Numerator - Quantity Per Pack	1
Initial Performance (IEC Compliant)		Numerator - Packs per outer box	1
Luminaire Lumens	9000	Material Nr. (12NC)	912401279118
		Net Weight (Piece)	0.001 kg
		Commercial Code	LBX90L840-UNV-UD
		Catalog Number Description	4', 9,000 Nominal Delivered Lumens, 4000K, 80 CRI, General Distribution, Oval Uplight Diffuse Lens
		Quick Ship	-

