



LBX LED Linear Suspended

4', 9,000 Nominal Delivered Lumens, 4000K, 80 CRI, General Distribution, Flat Diffuse Lens

4', 9,000 Nominal Delivered Lumens, 4000K, 80 CRI, General Distribution, Flat Diffuse Lens – 127 lm/W

The LBX LED linear suspended luminaires with optional LightBalance Optics provide the versatility required for a wide range of applications. Available in 5 different configurations, LBX is easy to install and can be mounted together in runs. Where precise control is required, LightBalance Optics put the light where it's needed. Choose between narrow, medium, wide, aisle, & double asymmetric distributions.

Product data

General Information		Initial Performance (IEC Compliant)	
Colour Temperature	4000 K	Luminaire Lumens	9000
CRI	80	Efficacy	127 lm/W
Photometric Distribution Type	Direct		
Mounting	Suspended		
Operating and Electrical		Product Data	
Voltages	347/UNIV V	Order product name	LBX90L840-UNV
Luminaire Input Watts	66	EAN/UPC - Product	784197191399
		Order code	LBX90L840-UNV-FD
		Numerator - Quantity Per Pack	1
		Numerator - Packs per outer box	1
		Material Nr. (12NC)	912401279119
		Net Weight (Piece)	0.001 kg
		Catalog Number	LBX90L840-UNV-FD
Mechanical and Housing			
Fixture Size	48 in		
Shape	Linear		

LBX LED Linear Suspended

Catalog Number	Description
	4', 9,000 Nominal Delivered Lumens, 4000K, 80 CRI, General Distribution, Flat Diffuse Lens

