



SofTrace Recessed LED

2STG36L840-4-DS-UNV

2x4, 3600 Nominal Delivered Lumens, 80 CRI, 4000K, Diffuse-Smooth

SofTrace LED brings new meaning to the concept of combining style with performance. Equipped with a fresh streamlined design and innovative technology, SofTrace provides a huge step forward for the lighting industry. The sleek profile design belies the true “horsepower under the hood”. With efficiency levels exceeding 95% and lumens per Watt as great as 87, an architectural product now delivers leading edge performance for the most environmentally conscious user.

Product data

General Information	
Color Temperature	4000K
CRI	80
Photometric Distribution Type	Direct
Mounting	Recessed
Operating and Electrical	
Voltages	120/277/347 V
Luminaire Input Watts	35
Mechanical and Housing	
Fixture Size	2 ft x 4 ft
Shape	Rectangular
Initial Performance (IEC Compliant)	
Luminaire Lumens	3600

Product Data	
Order product name	2STG36L840-4-DS-UNV
EAN/UPC - Product	781370740672
Order code	912401279208
Local order code	7074067
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	912401279208
Net Weight (Piece)	0.001 kg
Commercial Code	2STG36L840-4-DS-UNV-DIM
Catalog Number Description	2x4, 3600 Nominal Delivered Lumens, 80 CRI, 4000K, Diffuse-Smooth
Quick Ship	-