



SofTrace Recessed LED

2x4, 3600 Nominal Delivered Lumens, 80 CRI, 4000K, Diffuse-Smooth

2x4, 3600 Nominal Delivered Lumens, 80 CRI, 4000K, Diffuse-Smooth

SofTrace LED brings new meaning to the concept of combining style with performance. Equipped with a fresh streamlined design and innovative technology, SofTrace provides a huge step forward for the lighting industry. The sleek profile design belies the true “horsepower under the hood”. With efficiency levels exceeding 95% and lumens per Watt as great as 87, an architectural product now delivers leading edge performance for the most environmentally conscious user.

Product data

General Information		Shape	
Colour Temperature	4000K	Rectangular	
CRI	80	Initial Performance (IEC Compliant)	
Photometric Distribution Type	Direct	Luminaire Lumens	
Mounting	Recessed	3600	
Operating and Electrical		Product Data	
Voltages	120/277/347 V	Order product name	
Luminaire Input Watts	35	2STG36L840-4-DS-UNV	
Mechanical and Housing		EAN/UPC - Product	
Fixture Size	2 ft x 4 ft	781370740672	
		Order code	
		2STG36L840-4-DS-UNV-DIM	
		Numerator - Quantity Per Pack	
		1	
		Numerator - Packs per outer box	
		1	
		Material Nr. (12NC)	
		912401279208	
		Net Weight (Piece)	
		0.001 kg	

SofTrace Recessed LED

Catalog Number	2STG36L840-4-DS-UNV-DIM
Catalog Number Description	2x4, 3600 Nominal Delivered Lumens, 80 CRI, 4000K, Diffuse-Smooth

