



APX LED High Bay

24,000 Nominal Delivered Lumens, 4000K, 80 CRI, Wide Distribution, Frosted Acrylic Lens

24,000 Nominal Delivered Lumens, 4000K, 80 CRI, Wide Distribution, Frosted Acrylic Lens - 103 lm/W

The APX LED High Bay provides durability and high performance for your customer's demanding environments. The APX can be specified for many areas requiring a sealed luminaire, such as laboratories, food processing, parking areas, and other industrial applications. The rugged housing and clear or frosted lens options combine for durable and effective lighting that is also comfortable for the occupants. LED technology provides efficiency, long life, and reduces energy costs.

Product data

General Information		Efficacy	
Lamp Source Code	LED	103 lm/W	
Colour Temperature	4000 K	Product Data	
CRI	80	Order product name	APX24LL40-UNV
Photometric Distribution Type	Direct	EAN/UPC - Product	784197328849
Mounting	Suspended	Order code	APX24LL40-UNV-W-LFA
Operating and Electrical		Numerator - Quantity Per Pack	1
Voltages	120/208/240/277/347/480/UNIV V	Numerator - Packs per outer box	1
Luminaire Input Watts	191	Material Nr. (12NC)	912401281712
Mechanical and Housing		Net Weight (Piece)	0.001 kg
Fixture Size	48 in	Catalog Number	APX24LL40-UNV-W-LFA
Initial Performance (IEC Compliant)		Catalog Number Description	24,000 Nominal Delivered Lumens, 4000K, 80 CRI, Wide Distribution, Frosted Acrylic Lens
Luminaire Lumens	24000		