



ClearAppeal Recessed LED

1x4 Tunable White, 3000 Nominal Delivered Lumens, 80 CRI, 2700-6500K, Diffuse (Smooth)

1x4 Tunable White, 3000 Nominal Delivered Lumens, 80 CRI, 2700-6500K, Diffuse (Smooth) - 86 lm/W

ClearAppeal Recessed Architectural LED offers smooth brightness across the face of the luminaire and provides excellent visual comfort. Its modern architectural styling complements any space.

Product data

General Information	
Colour Temperature	6500K
CRI	80
Photometric Distribution Type	Direct
Mounting	Recessed
Operating and Electrical	
Voltages	120/277/347/UNIV V
Luminaire Input Watts	35
Mechanical and Housing	
Fixture Size	1 ft x 4 ft
Shape	Rectangular
Initial Performance (IEC Compliant)	
Luminaire Lumens	3000

Efficacy	86 lm/W
Product Data	
Order product name	1CAG30L8TW-4-DS-UNV
EAN/UPC - Product	784197259426
Order code	1CAG30L8TW-4-DS-UNV-DTW
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	912401282761
Net Weight (Piece)	0.001 kg
Catalog Number	1CAG30L8TW-4-DS-UNV-DTW
Catalog Number Description	1x4 Tunable White, 3000 Nominal Delivered Lumens, 80 CRI, 2700-6500K, Diffuse (Smooth)