



EvoGrid Recessed LED

2EVG32L8TW-2-D-UNV

2x2 Tunable White, 3200 Nominal Delivered Lumens, 80 CRI, 2700-6500K, Diffuse (Smooth) - 91 lm/W

EvoGrid Recessed Architectural LED provides general lighting perfect for a wide variety of applications. Its soft opal diffuser with large luminous area minimizes apparent brightness compared to other based luminaires.

Product data

| General Information | |
|-------------------------------------|--------------------|
| Color Temperature | 6500K |
| CRI | 80 |
| Photometric Distribution Type | Direct |
| Mounting | Recessed |
| Operating and Electrical | |
| Voltages | 120/277/347/UNIV V |
| Luminaire Input Watts | 35 |
| Mechanical and Housing | |
| Fixture Size | 2 ft x 2 ft |
| Shape | Square |
| Initial Performance (IEC Compliant) | |
| Luminaire Lumens | 3200 |
| Efficacy | 91 lm/W |

| Product Data | |
|---------------------------------|--|
| Order product name | 2EVG32L8TW-2-D-UNV |
| EAN/UPC - Product | 784197259488 |
| Order code | 912401282762 |
| Local order code | 9725948 |
| Numerator - Quantity Per Pack | 1 |
| Numerator - Packs per outer box | 1 |
| Material Nr. (12NC) | 912401282762 |
| Net Weight (Piece) | 0.001 kg |
| Commercial Code | 2EVG32L8TW-2-D-UNV-DTW |
| Catalog Number Description | 2x2 Tunable White, 3200 Nominal Delivered Lumens, 80 CRI, 2700-6500K, Diffuse (Smooth) |
| Quick Ship | - |