



# EvoGrid Recessed LED

**2x2 Tunable White, 3200 Nominal Delivered Lumens, 80 CRI, 2700-6500K, Diffuse (Smooth)**

2x2 Tunable White, 3200 Nominal Delivered Lumens, 80 CRI, 2700-6500K, Diffuse (Smooth) - 91 lm/W

EvoGrid Recessed Architectural LED provides general lighting perfect for a wide variety of applications. Its soft opal diffuser with large luminous area minimizes apparent brightness compared to other based luminaires.

## Product data

General Information	
Colour Temperature	6500K
CRI	80
Photometric Distribution Type	Direct
Mounting	Recessed
Operating and Electrical	
Voltages	120/277/347/UNIV V
Luminaire Input Watts	35
Mechanical and Housing	
Fixture Size	2 ft x 2 ft
Shape	Square
Initial Performance (IEC Compliant)	
Luminaire Lumens	3200

Efficacy	91 lm/W
Product Data	
Order product name	2EVG32L8TW-2-D-UNV
EAN/UPC - Product	784197259488
Order code	2EVG32L8TW-2-D-UNV-DTW
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	912401282762
Net Weight (Piece)	0.001 kg
Catalog Number	2EVG32L8TW-2-D-UNV-DTW
Catalog Number Description	2x2 Tunable White, 3200 Nominal Delivered Lumens, 80 CRI, 2700-6500K, Diffuse (Smooth)