



SofTrace Recessed LED

2x2 Tunable White, 3200 Nominal Delivered Lumens, 80 CRI, 2700-6500K, Diffuse (Smooth)

2x2 Tunable White, 3200 Nominal Delivered Lumens, 80 CRI, 2700-6500K, Diffuse (Smooth)

SofTrace LED brings new meaning to the concept of combining style with performance. Equipped with a fresh streamlined design and innovative technology, SofTrace provides a huge step forward for the lighting industry. The sleek profile design belies the true “horsepower under the hood”. With efficiency levels exceeding 95% and lumens per Watt as great as 87, an architectural product now delivers leading edge performance for the most environmentally conscious user.

Product data

General Information		Shape	
Colour Temperature	6500K	Square	
CRI	80	Initial Performance (IEC Compliant)	
Photometric Distribution Type	Direct	Luminaire Lumens	3200
Mounting	Recessed	Product Data	
Operating and Electrical		Order product name	2STG32L8TW-2-D-UNV
Voltages	120/277/347/UNIV V	EAN/UPC - Product	784197259495
Luminaire Input Watts	35	Order code	2STG32L8TW-2-D-UNV-DTW
Mechanical and Housing		Numerator - Quantity Per Pack	1
Fixture Size	2 ft x 2 ft	Numerator - Packs per outer box	1
		Material Nr. (12NC)	912401282763
		Net Weight (Piece)	0.001 kg

SofTrace Recessed LED

Catalog Number	2STG32L8TW-2-D-UNV-DTW
Catalog Number Description	2x2 Tunable White, 3200 Nominal Delivered Lumens, 80 CRI, 2700-6500K, Diffuse (Smooth)

