



Arioso Recessed Shallow

2AVEG228-ACR-UNV

2x4, 2 Lamp F28T5, Low - Profile Reflector & White Opal Acrylic Diffuser

The Philips Day-Brite / Philips CFI Arioso Recessed Shallow is ideal for shallow ceiling applications and offers simple clean lines in combination with soft natural illumination. With micro-perforated baskets and contoured seamless reflectors, this series focuses on providing smooth comfortable lighting while subtly complementing the space. Flexible enough to integrate with any architectural design, these luminaires provide a soft unassuming glow with comfortable illumination to optimize work and recreational activities.

Product data

General Information	
Lamp Envelope Code	T-5
Lamp Source Code	Fluorescent
Lamp Watts	28
Number of Lamps	2
Photometric Distribution Type	Direct
Mounting	Recessed
Operating and Electrical	
Voltages	UNIV V
Mechanical and Housing	
Fixture Size	2 ft x 4 ft
Shape	Rectangular

Product Data	
Order product name	2AVEG228-ACR-UNV
EAN/UPC - Product	784197027780
Order code	912401289210
Local order code	9702778
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	912401289210
Net Weight (Piece)	8.171 kg
Commercial Code	2AVEG228-ACR-UNV-1/2-EB
Catalog Number Description	2x4, 2 Lamp F28T5, Low Profile Reflector & White Opal Acrylic Diffuser
Quick Ship	-