



Ariosso Recessed Shallow

2x4, 2 Lamp F28T5, Low Profile Reflector & White Opal Acrylic Diffuser

2x4, 2 Lamp F28T5, Low - Profile Reflector & White Opal Acrylic Diffuser

The Day-Brite / CFI Ariosso Recessed Shallow is ideal for shallow ceiling applications and offers simple clean lines in combination with soft natural illumination. With micro-perforated baskets and contoured seamless reflectors, this series focuses on providing smooth comfortable lighting while subtly complementing the space. Flexible enough to integrate with any architectural design, these luminaires provide a soft unassuming glow with comfortable illumination to optimize work and recreational activities.

Product data

General Information		Mechanical and Housing	
Lamp Envelope Code	T-5	Fixture Size	2 ft x 4 ft
Lamp Source Code	Fluorescent	Shape	Rectangular
Lamp Watts	28		
Number of Lamps	2		
Photometric Distribution Type	Direct		
Mounting	Recessed		
Operating and Electrical		Product Data	
Voltages	UNIV V	Order product name	2AVEG228-ACR-UNV
		EAN/UPC - Product	784197027780
		Order code	2AVEG228-ACR-UNV-1/2-EB
		Numerator - Quantity Per Pack	1
		Numerator - Packs per outer box	1
		Material Nr. (12NC)	912401289210
		Net Weight (Piece)	8.171 kg

Arioso Recessed Shallow

Catalog Number	2AVEG228-ACR-UNV-1/2-EB
Catalog Number Description	2x4, 2 Lamp F28T5, Low Profile Reflector & White Opal Acrylic Diffuser

