



BL711 Micro Accent

Accent, Aluminum Bullyte w/ Stake, Black, 2W LED, 12V

Accent, Aluminum Bullyte w/ Stake, Black, 2W LED, 12V - 100 lm/W

The BL711 Mini-Bullyte is an excellent choice for limited space applications. It's all aluminum construction includes a fully-adjustable swivel arm with vibration-proof locking teeth. Optics include a clear tempered glass lens and requires a 20W T3 or 35W maximum MR11. Energy saving LED is available to ensure even light distribution and long life.

Product data

General information	
Lamp Source Code	LED
Lamp Watts	2
Number of Lamps	1
Colour Temperature	3000 K
CRI	80
Photometric Distribution Type	General Diffuse
Mounting	NPT/NPS
Number Of Pieces	1
Operating and electrical	
Voltages	12 V
Luminaire Input Watts	2
Conduit Connection	7/8 inch knockout

Mechanical and housing	
Enclosure	Metal and Plastic
Initial performance (IEC compliant)	
Luminaire Lumens	200
Efficacy	100 lm/W
Product data	
Order product name	BULLYTE,MICRO,12V,LED,T3 LMP,STK
EAN/UPC - Product	783352020307
Order code	BL711-AS7LED2W
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	912401335008
Net Weight (Piece)	0.001 kg
Catalog Number	BL711-AS7LED2W

BL711 Micro Accent

Catalog Number	Description
	Accent, Aluminum Bullyte w/ Stake, Black, 2W LED, 12V

