



BUL16 Micro Accent

Accent, Ultem Composite Bullyte w/ Stake & Lamp, Bronze, 7W LED, Flood

Accent, Ultem Composite Bullyte w/ Stake & Lamp, Bronze, 7W LED, Flood

The BUL16 is a low voltage composite Bullyte used for accent lighting and available with a 35W maximum MR16 bi-pin lamp or a Philips MR16 LED lamp. Construction includes a one-piece injection molded ULTEM® High Performance Polymer composite with fully rotatable shroud and a fully-adjustable swivel arm with vibration-proof locking teeth. Optics have a clear tempered glass affixed at 10° angle for natural cleaning.

Product data

General Information		Product Data	
Lamp Source Code	LED	Order product name	ACCENT,COMP,12V,LED,MR16 LMP,STK
Lamp Watts	7	Order code	BUL16-GS7LED7FLW
Number of Lamps	1	Numerator - Quantity Per Pack	1
Colour Temperature	3000K	Numerator - Packs per outer box	1
CRI	80	Material Nr. (12NC)	912401335036
Photometric Distribution Type	Medium	Net Weight (Piece)	0.100 kg
Mounting	NPT/NPS	Catalog Number	BUL16-GS7LED7FLW
Operating and Electrical		Catalog Number Description	Accent, Ultem Composite Bullyte w/ Stake & Lamp, Bronze, 7W LED, Flood
Voltages	12 V		
Luminaire Input Watts	7		
Initial Performance (IEC Compliant)			
Luminaire Lumens	600		