



BL616 Micro Accent

ACCENT,MICRO,12V,LED,MR16 LMP,STK

Accent, Aluminum w/ Stake, Verde, 7W LED, Narrow Flood

The BL616 is made with die-cast aluminum and has a fully adjustable swivel arm with vibration-proof locking teeth. Available in low voltage incandescent and LED sources.

Product data

General Information	
Lamp Source Code	LED
Lamp Watts	7
Number of Lamps	1
Color Temperature	3000K
CRI	80
Photometric Distribution Type	Medium
Mounting	NPT/NPS
Operating and Electrical	
Voltages	12 V
Luminaire Input Watts	7
Initial Performance (IEC Compliant)	
Luminaire Lumens	600

Product Data	
Order product name	ACCENT,MICRO,12V,LED,MR16 LMP,STK
Order code	BL616-GS7LED7NFW
Local order code	.
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	912401335045
Net Weight (Piece)	0.100 kg
Commercial Code	BL616-GS7LED7NFW
Catalog Number Description	Accent, Aluminum w/ Stake, Verde, 7W LED, Narrow Flood
Quick Ship	-