



BL616 Micro Accent

Accent, Aluminum w/ Stake, Verde, 7W LED, Narrow Flood

Accent, Aluminum w/ Stake, Verde, 7W LED, Narrow Flood

The BL616 is made with die-cast aluminum and has a fully adjustable swivel arm with vibration-proof locking teeth. Available in low voltage incandescent and LED sources.

Product data

General information	
Lamp Source Code	LED
Lamp Watts	7
Number of Lamps	1
Colour Temperature	3000 K
CRI	80
Photometric Distribution Type	Medium
Mounting	NPT/NPS

Operating and electrical	
Voltages	12 V
Luminaire Input Watts	7
Conduit Connection	7/8 inch knockout

Initial performance (IEC compliant)	
Luminaire Lumens	600

Product data	
Order product name	ACCENT,MICRO,12V,LED,MR16 LMP,STK
Order code	BL616-GS7LED7NFW
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	912401335045
Net Weight (Piece)	0.100 kg
Catalog Number	BL616-GS7LED7NFW
Catalog Number Description	Accent, Aluminum w/ Stake, Verde, 7W LED, Narrow Flood