



BL16 Micro Accent

ACCENT,BRASS,12V,LED,MR16 LMP

Accent w/ Stake & Lamp, Brass, 7W LED, Narrow Flood

Hadco's BL16 is a low voltage brass bullet used for accent lighting. It's made from die cast brass and has a fully rotatable shroud with gasket. Optics include a clear tempered glass affixed at 10° angle for natural cleaning with a 50W maximum MR16 bi-pin lamp. Also available with a Philips MR16 LED lamp

Product data

| General Information | |
|-------------------------------------|---------|
| Lamp Source Code | LED |
| Lamp Watts | 7 |
| Number of Lamps | 1 |
| Color Temperature | 3000K |
| CRI | 80 |
| Photometric Distribution Type | Medium |
| Mounting | NPT/NPS |
| Operating and Electrical | |
| Voltages | 12 V |
| Luminaire Input Watts | 7 |
| Initial Performance (IEC Compliant) | |
| Luminaire Lumens | 600 |

| Product Data | |
|---------------------------------|---|
| Order product name | ACCENT,BRASS,12V,LED,MR16 LMP |
| Order code | BL16-NS7LED7NFW |
| Local order code | . |
| Numerator - Quantity Per Pack | 1 |
| Numerator - Packs per outer box | 1 |
| Material Nr. (12NC) | 912401335046 |
| Net Weight (Piece) | 0.100 kg |
| Commercial Code | BL16-NS7LED7NFW |
| Catalog Number Description | Accent w/ Stake & Lamp, Brass, 7W LED, Narrow Flood |
| Quick Ship | - |