



BL16 Micro Accent

Accent w/ Stake & Lamp, Brass, 7W LED, Narrow Flood

Accent w/ Stake & Lamp, Brass, 7W LED, Narrow Flood

Hadco's BL16 is a low voltage brass bullet used for accent lighting. It's made from die cast brass and has a fully rotatable shroud with gasket. Optics include a clear tempered glass affixed at 10° angle for natural cleaning with a 50W maximum MR16 bi-pin lamp. Also available with a Philips MR16 LED lamp

Product data

General Information	
Lamp Source Code	LED
Lamp Watts	7
Number of Lamps	1
Colour Temperature	3000K
CRI	80
Photometric Distribution Type	Medium
Mounting	NPT/NPS
Operating and Electrical	
Voltages	12 V
Luminaire Input Watts	7
Initial Performance (IEC Compliant)	
Luminaire Lumens	600

Product Data	
Order product name	ACCENT,BRASS,12V,LED,MR16 LMP
Order code	BL16-NS7LED7NFW
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	912401335046
Net Weight (Piece)	0.100 kg
Catalog Number	BL16-NS7LED7NFW
Catalog Number Description	Accent w/ Stake & Lamp, Brass, 7W LED, Narrow Flood