



iUL516 Inground

INGROUND,MICRO,12V,LED,MR16 LMP

Inground, Composite, Narrow Flood, Bronze, 7W LED, 3000K, 12V

Hadco's iUL516 is a compact low voltage composite landscape luminaire for inground applications. Lamping sources include 35W maximum MR16 bi-pin lamp and LED. Construction includes a one-piece injection molded ULTEM® High Performance Polymer composite body with a single piece injected lens ring and gasketed lens. Twist-off operation for ease of maintenance.

Product data

General Information	
Lamp Source Code	LED
Lamp Watts	7
Number of Lamps	1
Color Temperature	3000K
CRI	80
Photometric Distribution Type	Medium
Mounting	In Ground
Operating and Electrical	
Voltages	12 V
Luminaire Input Watts	7
Initial Performance (IEC Compliant)	
Luminaire Lumens	600

Product Data	
Order product name	INGROUND,MICRO,12V,LED,MR16 LMP
Order code	IUL516-HLED7NFW
Local order code	.
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	912401335049
Net Weight (Piece)	0.001 kg
Commercial Code	IUL516-HLED7NFW
Catalog Number Description	Inground, Composite, Narrow Flood, Bronze, 7W LED, 3000K, 12V
Quick Ship	Service Smart (2 Days) USA