



# CPL12 Path Light

Path Light, Aluminum w/Stake, Bronze, 2W LED, 12V

Path Light, Aluminum w/Stake, Bronze, 2W LED, 12V – 100 lm/W

The Hadco CPL series is a simply-crafted low voltage path light available in two distinctive lighting heads. It includes a die-cast aluminum with twist-lock top for tool-less relamping and Single-piece molded silicone gasket to prevent water, dust, and insect filtration.

## Product data

General information	
Lamp Source Code	LED
Lamp Watts	2
Number of Lamps	1
Colour Temperature	3000 K
CRI	80
Photometric Distribution Type	General Diffuse
Mounting	NPT/NPS
Number Of Pieces	1
Operating and electrical	
Voltages	12 V
Luminaire Input Watts	2
Conduit Connection	7/8 inch knockout
Mechanical and housing	
Enclosure	Metal and Plastic

Initial performance (IEC compliant)	
Luminaire Lumens	200
Efficacy	100 lm/W
Product data	
Order product name	PATHLIGHT,12V,2W,LED,STAKE
EAN/UPC - Product	783352022851
Order code	CPL12-HS7LED2W
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	912401335071
Net Weight (Piece)	0.001 kg
Catalog Number	CPL12-HS7LED2W
Catalog Number Description	Path Light, Aluminum w/Stake, Bronze, 2W LED, 12V