



# CUL6 Path Light

Path Light, w/ Stake, Copper, 2W LED, 3000K, 12V, CUL6

Path Light, w/ Stake, Copper, 2W LED, 3000K, 12V, CUL6 - 100 lm/W

Hadco's CUL family of path lights are low voltage landscape luminaires offering a distinctive appearance to any outdoor application. The fixtures are hand crafted with a spun solid copper roof with copper stem. Optics includes a reflective white powdercoat on underside of roof with frosted tempered glass lens. Sources include standard low voltage lamps and LED that offers 50,000 hours of operating life, has a CCT of 3,000K or 4,000K and a CRI of 80.

## Product data

General information	
Lamp Source Code	LED
Lamp Watts	2
Number of Lamps	1
Colour Temperature	3000 K
CRI	80
Photometric Distribution Type	General Diffuse
Mounting	NPT/NPS
Number Of Pieces	1
Operating and electrical	
Voltages	12 V
Luminaire Input Watts	2
Conduit Connection	7/8 inch knockout

Mechanical and housing	
Enclosure	Metal and Plastic
Initial performance (IEC compliant)	
Luminaire Lumens	200
Efficacy	100 lm/W
Product data	
Order product name	PATH,COPPER,12V,LED,T3 LMP,STK
Order code	CUL6-S7LED2W
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	912401335075
Net Weight (Piece)	0.100 kg
Catalog Number	CUL6-S7LED2W

# CUL6 Path Light

Catalog Number	Description
	Path Light, w/ Stake, Copper, 2W LED, 3000K, 12V, CUL6

