



CUL7 Path Light

PATH,COPPER,12V,LED,T3 LMP,STK

Path Light, w/ Stake, Copper, 2W LED, 3000K, 12V

Hadco's CUL family of path lights are low voltage landscape luminaires offering a distinctive appearance to any outdoor application. The fixtures are hand crafted with a spun solid copper roof with copper stem. Optics includes a reflective white powdercoat on underside of roof with frosted tempered glass lens. Sources include standard low voltage lamps and LED that offers 50,000 hours of operating life, has a CCT of 3,000K or 4,000K and a CRI of 80.

Product data

General Information	
Lamp Source Code	LED
Lamp Watts	2
Number of Lamps	1
Color Temperature	3000K
CRI	80
Photometric Distribution Type	General Diffuse
Mounting	NPT/NPS
Operating and Electrical	
Voltages	12 V
Luminaire Input Watts	2
Initial Performance (IEC Compliant)	
Luminaire Lumens	200

Product Data	
Order product name	PATH,COPPER,12V,LED,T3 LMP,STK
Order code	CUL7-S7LED2W
Local order code	.
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	912401335080
Net Weight (Piece)	0.100 kg
Commercial Code	CUL7-S7LED2W
Catalog Number Description	Path Light, w/ Stake, Copper, 2W LED, 3000K, 12V
Quick Ship	-