



CitySoul poles and brackets

YHB530 PL-FLG 3500 76 RAL PD-TRI

Pole with flange, 3.5 m, 75 mm, RAL color

CitySoul gen2 is one of the most versatile and inspirational urban street lighting families designed by Philips to date. This highly efficient range delivers excellent lighting levels whilst also providing the right ambiance for all urban application areas, from the outskirts of the city right through to the city center. By evolving the modularity of the CitySoul family and adding new innovations like the Lyre and the Accent bracket, Philips has made this range the ideal toolbox for every urban context. The design is flatter, completely round, and the transitions with the spigot and bracket entirely flush, thereby giving your cityscape a coherent, elegant and discreet identity. Designed around its LED engine, CitySoul gen2 is highly efficient and easy to maintain. It comes in two sizes and is suitable for side-entry, post-top, catenary and suspended mounting.

Product data

General Information	
Pole type	Pole with flange
Pole color	RAL color
Value ladder	Specification
Mechanical and Housing	
Fixation point length distance (Nom)	70 mm
Fixation diameter	Mounting device diameter 60 mm
Pole top diameter	75 mm
Pole height	3.5 m

Product Data	
Order product name	YHB530 PL-FLG 3500 76 RAL PD-TRI
Full product name	YHB530 PL-FLG 3500 76 RAL PD-TRI
Full product code	871869693254400
Order code	912401451147
Material Nr. (12NC)	912401451147
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696932544
Numerator - Packs per outer box	1
EAN/UPC - Case	8718696932544

Dimensional drawing

