



# MileWide² Pole

## YRP435 PLT-FLG CONE 6000 RAL 60/60

Pole with flange, 6.0 m, 80 mm, RAL color

Many municipal authorities are embracing the benefits of contemporary outdoor lighting. These include a more attractive urban environment and increased comfort, safety and security for the public. Not to mention the positive impact on environmental protection and city branding. Together with Holscher Design, Philips has developed MileWide², the successor to the highly popular MileWide family. Featuring a range of dedicated masts and brackets, the pure, clean design of MileWide² integrates perfectly with today's and tomorrow's cityscape. With its high-quality finish and high level of lighting performance, MileWide² is suitable for a wide range of applications, ranging from traffic roads to city centers. Multi-layer optics provide a uniform light distribution and reduced glare, enabling direct replacement of HID solutions without compromising on spacing, mounting height or light quality.

### Product data

General Information		Full product name	
Pole type	Pole with flange	Full product code	YRP435 PLT-FLG CONE 6000 RAL 60/60
Pole color	RAL color	Order code	871869938161500
Value ladder	Specification	Material Nr. (12NC)	912401451652
Mechanical and Housing		Numerator - Quantity Per Pack	912401451652
Fixation diameter	Mounting device diameter 60 mm and 60 mm	EAN/UPC - Product/Case	1
Pole top diameter	80 mm	Numerator - Packs per outer box	8718699381615
Pole height	6.0 m	EAN/UPC - Case	912401451652
Product Data		1	
Order product name	YRP435 PLT-FLG CONE 6000 RAL 60/60	8718699381615	

## MileWide<sup>2</sup> Pole

### Dimensional drawing

