



FluxPanel LED

2FXP42B840-4-DS-UNV (2 PACKS ONLY)

2x4, 4200 Nominal Delivered Lumens, 80 CRI, 4000K, Diffuse - 112 lm/W

Philips Day-Brite/Philips CFI FluxPanel LED recessed is a highly versatile luminaire designed to provide smooth lighting gradient on the lens surface and ease of installation. Available for use in recessed, suspended, and surface mount orientation, FluxPanel is ideal for general lighting applications such as open office, schools, healthcare, and retail.

Product data

General Information	
Colour Temperature	4000K
CRI	80
Mounting	Recessed frange vertaling Surface Suspended
Operating and Electrical	
Voltages	120/277/347/UNIV V
Luminaire Input Watts	38
Mechanical and Housing	
Fixture Size	2 ft x 4 ft
Shape	Rectangular
Approval and Application	
DesignLights Consortium Qualified Product List	DesignLights Consortium Qualified Product List
Initial Performance (IEC Compliant)	
Luminaire Lumens	4200

Efficacy	112 lm/W
Product Data	
Order product name	2FXP42B840-4-DS-UNV (2 PACKS ONLY)
EAN/UPC - Product	784197381325
Order code	912401454792
Local order code	.
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	2
Material Nr. (12NC)	912401454792
Net Weight (Piece)	6.540 kg
Commercial Code	2FXP42B835-4-DS-UNV-DIM
Catalog Number Description	2x4, 4200 Nominal Delivered Lumens, 80 CRI, 4000K, Diffuse
Quick Ship	Service Smart (2 Days) North America