



# SofTrace Recessed LED

## 1STG38B840-4-D-UNV

1x4, 3800 Nominal Delivered Lumens, 80 CRI, 4000K, Diffuse-Smooth - 113 lm/W

SofTrace LED brings new meaning to the concept of combining style with performance. Equipped with a fresh streamlined design and innovative technology, SofTrace provides a huge step forward for the lighting industry. The sleek profile design belies the true “horsepower under the hood”. With efficiency levels exceeding 95% and lumens per Watt as great as 87, an architectural product now delivers leading edge performance for the most environmentally conscious user.

### Product data

General Information	
Color Temperature	4000K
CRI	80
Photometric Distribution Type	Direct
Mounting	Recessed
Operating and Electrical	
Voltages	120/277/347 V
Luminaire Input Watts	34
Mechanical and Housing	
Fixture Size	1 ft x 4 ft
Shape	Rectangular
Approval and Application	
DesignLights Consortium Qualified Product List	DesignLights Consortium Qualified Product List

Initial Performance (IEC Compliant)	
Luminaire Lumens	3800
Efficacy	113 lm/W
Product Data	
Order product name	1STG38B840-4-D-UNV
EAN/UPC - Product	784197610098
Order code	912401456759
Local order code	9761009
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	912401456759
Net Weight (Piece)	0.001 kg
Commercial Code	1STG38B840-4-D-UNV-DIM
Catalog Number Description	1x4, 3800 Nominal Delivered Lumens, 80 CRI, 4000K, Diffuse-Smooth
Quick Ship	-

## SofTrace Recessed LED

---

