



# ClearAppeal Recessed LED

## 2CAG40B840-4-DS-UNV

2x4, 4000 Nominal Delivered Lumens, 80 CRI, 4000K, Diffuse (Smooth), Dimming Driver - 121 lm/W

ClearAppeal Recessed Architectural LED offers smooth brightness across the face of the luminaire and provides excellent visual comfort. Its modern architectural styling complements any space.

### Product data

General Information		Initial Performance (IEC Compliant)	
Color Temperature	4000K	Luminaire Lumens	4000
CRI	80	Efficacy	121 lm/W
Photometric Distribution Type	Direct		
Mounting	Recessed		
Operating and Electrical		Product Data	
Voltages	347/UNIV V	Order product name	2CAG40B840-4-DS-UNV
Luminaire Input Watts	32	EAN/UPC - Product	784197610449
		Order code	912401456767
		Local order code	9761044
		Numerator - Quantity Per Pack	1
		Numerator - Packs per outer box	1
		Material Nr. (12NC)	912401456767
		Net Weight (Piece)	0.001 kg
		Commercial Code	2CAG40B840-4-DS-UNV-DIM
		Catalog Number Description	2x4, 4000 Nominal Delivered Lumens, 80 CRI, 4000K, Diffuse (Smooth), Dimming Driver
		Quick Ship	-
Mechanical and Housing			
Fixture Size	2 ft x 4 ft		
Shape	Rectangular		
Approval and Application			
DesignLights Consortium Qualified Product List	DesignLights Consortium Qualified Product List		

