



ClearAppeal Recessed LED

1x4, 3600 Nominal Delivered Lumens, 80 CRI, 4000K, Diffuse (Smooth), Dimming Driver

1x4, 3600 Nominal Delivered Lumens, 80 CRI, 4000K, Diffuse (Smooth), Dimming Driver – 108 lm/W

ClearAppeal Recessed Architectural LED offers smooth brightness across the face of the luminaire and provides excellent visual comfort. Its modern architectural styling complements any space.

Product data

General Information	
Colour Temperature	4000K
CRI	80
Photometric Distribution Type	Direct
Mounting	Recessed
Operating and Electrical	
Voltages	347/UNIV V
Luminaire Input Watts	34
Mechanical and Housing	
Fixture Size	1 ft x 4 ft
Shape	Rectangular

Approval and Application	
DesignLights Consortium Qualified	DesignLights Consortium Qualified Product
Product List	List

Initial Performance (IEC Compliant)	
Luminaire Lumens	3600
Efficacy	108 lm/W

Product Data	
Order product name	1CAG36B840-4-DS-UNV
EAN/UPC - Product	784197610609
Order code	1CAG36B840-4-DS-UNV-DIM
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	912401456771
Net Weight (Piece)	0.001 kg

ClearAppeal Recessed LED

Catalog Number	1CAG36B840-4-DS-UNV-DIM
Catalog Number Description	1x4, 3600 Nominal Delivered Lumens, 80 CRI, 4000K, Diffuse (Smooth), Dimming Driver

