



ClearAppeal Recessed LED

2CAG33B840-2-DS-UNV

2x2, 3300 Nominal Delivered Lumens, 80 CRI, 4000K, Diffuse (Smooth), Dimming Driver - 100 lm/W

ClearAppeal Recessed Architectural LED offers smooth brightness across the face of the luminaire and provides excellent visual comfort. Its modern architectural styling complements any space.

Product data

General Information		Product Data	
Color Temperature	4000K	Order product name	2CAG33B840-2-DS-UNV
CRI	80	EAN/UPC - Product	784197610623
Photometric Distribution Type	Direct	Order code	912401456773
Mounting	Recessed	Local order code	9761062
Operating and Electrical		Numerator - Quantity Per Pack	1
Voltages	347/UNIV V	Numerator - Packs per outer box	1
Luminaire Input Watts	34	Material Nr. (12NC)	912401456773
Mechanical and Housing		Net Weight (Piece)	0.001 kg
Fixture Size	2 ft x 2 ft	Commercial Code	2CAG33B840-2-DS-UNV-DIM
Shape	Square	Catalog Number Description	2x2, 3300 Nominal Delivered Lumens, 80 CRI, 4000K, Diffuse (Smooth), Dimming Driver
Initial Performance (IEC Compliant)		Quick Ship	-
Luminaire Lumens	3300		
Efficacy	100 lm/W		