



WP Wall Pack Large LED

WP Wallpack, 72 LEDs, 530mA, 4000K

WP Wallpack, 72 LEDs, 530mA, 4000K – 57 lm/W

The Stonco LED wallpack large WP offers maximum light output for general purpose area and security lighting through a classic glass refractor design. Now available with enhanced the Philips LEDGINE platform, WP LED provides improved energy savings compared with the former LED design. This versatile luminaire is ideal to match existing fixtures or retrofit HID legacy designs.

Product data

General Information	
Lamp source code	LED
Lamp wattage	65
Colour Temperature	4000 K
CRI	70
Photometric distribution type	Type IV
Mounting	Wall
Operating and Electrical	
Voltages	120/208/240/277/347/480/UNIV V
Luminaire input watts	65
Initial Performance (IEC Compliant)	
Luminaire lumens	6726

Efficacy	57 lm/W
Product Data	
Order product name	WP-LED-72L-530-NW-UNV-BZ
Order code	WP-LED-72L-530-NW-UNV-BZ
SAP numerator – quantity per pack	1
Numerator – packs per outer box	1
SAP material	912401463592
SAP net weight (piece)	0.001 kg
Commercial Code	WP-LED-72L-530-NW-UNV-BZ
Catalogue number description	WP Wallpack, 72 LEDs, 530mA, 4000K