



# WP Wall Pack Large LED

## WP Wallpack, 72 LEDs, 530mA, 4000K

WP Wallpack, 72 LEDs, 530mA, 4000K - 57 lm/W

The Stonco LED wallpack large WP offers maximum light output for general purpose area and security lighting through a classic glass refractor design. Now available with enhanced the Philips LEDGINE platform, WP LED provides improved energy savings compared to the former LED design. This versatile luminaire is ideal to match same as existing or retrofit HID legacy designs.

### Product data

General Information	
Lamp Source Code	LED
Lamp Watts	65
Colour Temperature	4000K
CRI	70
Mounting	Wall
Operating and Electrical	
Voltages	120/208/240/277/347/480/UNIV V
Luminaire Input Watts	65
Initial Performance (IEC Compliant)	
Luminaire Lumens	6726

Efficacy	57 lm/W
Product Data	
Order product name	WP-LED-72L-530-NW-UNV-BZ
Order code	WP-LED-72L-530-NW-UNV-BZ
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	912401463592
Net Weight (Piece)	0.001 kg
Catalog Number	WP-LED-72L-530-NW-UNV-BZ
Catalog Number Description	WP Wallpack, 72 LEDs, 530mA, 4000K