



# LED General Purpose Floods FL

LED, 40W, 4000K, Wide Flood Optics, Textured Dark Bronze

LED, 40W, 4000K, Wide Flood Optics, Textured Dark Bronze – 113 lm/W

The General Purpose LED Floodlights offer energy saving LED technology for long life and reduced maintenance. Versatile and stylish with five different sizes to choose from provides application flexibility for ground mount, wall mount, or pole mount installations. Ideal for sign lighting, building facades, security lighting, and general purpose floodlighting applications.

## Product data

General information	
Lamp Source Code	LED
Colour Temperature	4000 K
CRI	80
Photometric Distribution Type	NEMA 7H x 6V
Mounting	NPT/NPS
Number Of Pieces	1
Grade	Value Grade

Operating and electrical	
Voltages	120/208/240/277 V
Luminaire Input Watts	39
Conduit Connection	7/8 inch knockout

Mechanical and housing	
Shape	Rectangular
Material	Aluminum
Enclosure	Metal and Plastic

Approval and application	
Safety Listing	UL
Energy Certifications	DLC Standard cULus
IP Rating	IP66 [ Dust penetration-protected, jet-proof]
Vibration Rating	1.5G

Initial performance (IEC compliant)	
Luminaire Lumens	4433

LED General Purpose Floods FL

Efficacy	113 lm/W
Application conditions	
Ambient temperature range	-40 °C to 40 °C
Max Ambient Temp	40 °C
Min Ambient Temp	-40 °C
Min Ambient Temp-DUP(do not use)	-40 °C
Product data	
Order product name	FL40-NW-G1-K-FL-8-BZ
EAN/UPC - Product	783352024169

Order code	FL40-NW-G1-K-FL-8-BZ
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	912401467972
Net Weight (Piece)	3.120 kg
Catalog Number	FL40-NW-G1-K-FL-8-BZ
Catalog Number Description	LED, 40W, 4000K, Wide Flood Optics, Textured Dark Bronze

