



LED General Purpose Floods FL

LED, 300W, 4000K, Wide Flood Optics, Textured Dark Bronze

LED, 300W, 4000K, Wide Flood Optics, Textured Dark Bronze – 113 lm/W

The General Purpose LED Floodlights offer energy saving LED technology for long life and reduced maintenance. Versatile and stylish with five different sizes to choose from provides application flexibility for ground mount, wall mount, or pole mount installations. Ideal for sign lighting, building facades, security lighting, and general purpose floodlighting applications.

Product data

| General information | |
|-------------------------------|-----------------------------|
| Lamp Source Code | LED |
| Colour Temperature | 4000 K |
| CRI | 80 |
| Photometric Distribution Type | NEMA 7H x 7V |
| Mounting | Surface Ground / Floor Wall |
| Number Of Pieces | 1 |
| Grade | Value Grade |
| Operating and electrical | |
| Voltages | 120/208/240/277 V |
| Luminaire Input Watts | 301 |
| Conduit Connection | 7/8 inch knockout |

| Mechanical and housing | |
|-------------------------------------|---|
| Shape | Rectangular |
| Material | Aluminum |
| Enclosure | Metal and Plastic |
| Approval and application | |
| Safety Listing | UL |
| Energy Certifications | DLC Standard cULus |
| IP Rating | IP66 [Dust penetration-protected, jet-proof] |
| Initial performance (IEC compliant) | |
| Luminaire Lumens | 34025 |
| Efficacy | 113 lm/W |

LED General Purpose Floods FL

| | |
|----------------------------------|-----------------------|
| Application conditions | |
| Ambient temperature range | -40 °C to 40 °C |
| Max Ambient Temp | 40 °C |
| Min Ambient Temp | -40 °C |
| Min Ambient Temp-DUP(do not use) | -40 °C |
| Product data | |
| Order product name | FL300-NW-G1-T-FL-8-BZ |
| EAN/UPC - Product | 783352024190 |
| Order code | FL300-NW-G1-T-FL-8-BZ |

| | |
|---------------------------------|---|
| Numerator - Quantity Per Pack | 1 |
| Numerator - Packs per outer box | 1 |
| Material Nr. (12NC) | 912401467975 |
| Net Weight (Piece) | 17.200 kg |
| Catalog Number | FL300-NW-G1-T-FL-8-BZ |
| Catalog Number Description | LED, 300W, 4000K, Wide Flood Optics, Textured Dark Bronze |

