



LED General Purpose Floods FL

LED, 150W, 4000K, Wide Flood Optics, Textured Dark Bronze

LED, 150W, 4000K, Wide Flood Optics, Textured Dark Bronze – 112 lm/W

The General Purpose LED Floodlights offer energy saving LED technology for long life and reduced maintenance. Versatile and stylish with five different sizes to choose from provides application flexibility for ground mount, wall mount, or pole mount installations. Ideal for sign lighting, building facades, security lighting, and general purpose floodlighting applications.

Product data

General information	
Lamp Source Code	LED
Colour Temperature	4000 K
CRI	80
Photometric Distribution Type	NEMA 7H x 7V
Mounting	Surface Ground / Floor Wall
Number Of Pieces	1
Grade	Value Grade
Operating and electrical	
Voltages	347 V
Luminaire Input Watts	146
Conduit Connection	7/8 inch knockout

Mechanical and housing	
Shape	Rectangular
Material	Aluminum
Enclosure	Metal and Plastic
Approval and application	
Safety Listing	UL
Energy Certifications	DLC Standard cULus
IP Rating	IP66 [Dust penetration-protected, jet-proof]
Initial performance (IEC compliant)	
Luminaire Lumens	16325
Efficacy	112 lm/W

LED General Purpose Floods FL

Application conditions	
Ambient temperature range	-40 °C to 40 °C
Max Ambient Temp	40 °C
Min Ambient Temp	-40 °C
Min Ambient Temp-DUP(do not use)	-40 °C
Product data	
Order product name	FL150-NW-G1-T-FL-6-BZ
EAN/UPC - Product	783352024237
Order code	FL150-NW-G1-T-FL-6-BZ

Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	912401467979
Net Weight (Piece)	11.000 kg
Catalog Number	FL150-NW-G1-T-FL-6-BZ
Catalog Number Description	LED, 150W, 4000K, Wide Flood Optics, Textured Dark Bronze

