



# Area Light LED

## Area Light, 150W, 4000K, Type 3, 120-277V, Arm Mount, Bronze

Area Light, 150W, 4000K, Type 3, 120-277V, Arm Mount, Bronze  
- 126 lm/W

The Area Light LED features energy saving LED technology ideal for pole mounted area lighting applications. Area Light LED is available with Type 3 and Type 4 distributions in two lumen packages, providing up to 25,000 lumens.

### Product data

General information		Energy Certifications	DLC Standard
Lamp Source Code	LED	<b>Initial performance (IEC compliant)</b>	
Colour Temperature	4000 K	Luminaire Lumens	18500
CRI	70	Efficacy	126 lm/W
Photometric Distribution Type	Type III	<b>Application conditions</b>	
Mounting	Pole Arm	Ambient temperature range	-40 to +40 °C
B.U.G. Rating	B3U0G3	Max Ambient Temp	+40 °C
Awards	DLC QPL	Min Ambient Temp	-40 °C
<b>Operating and electrical</b>		Min Ambient Temp-DUP(do not use)	-40 °C
Voltages	120/208/240/277 V	<b>Product data</b>	
Luminaire Input Watts	147	Order product name	AL150-NW-G1-AR-3-8-BZ
Conduit Connection	7/8 inch knockout	EAN/UPC - Product	783352023971
<b>Mechanical and housing</b>		Order code	AL150-NW-G1-AR-3-8-BZ
Shape	Rectangular	Numerator - Quantity Per Pack	1
<b>Approval and application</b>		Numerator - Packs per outer box	1
Safety Listing	UL	Material Nr. (12NC)	912401467981

## Area Light LED

---

<b>Net Weight (Piece)</b>	7.000 kg
<b>Catalog Number</b>	AL150-NW-G1-AR-3-8-BZ
<b>Catalog Number Description</b>	Area Light, 150W, 4000K, Type 3, 120-277V, Arm Mount, Bronze

---

