



# LED General Purpose Garage & Canopy GC

LED, 40W, 4000K, Type 5 Optics, Textured Dark Bronze

LED, 40W, 4000K, Type 5 Optics, Textured Dark Bronze – 128 lm/W

The LED Garage and Canopy light is slim and durable with a lightweight design, and provides you with a visually appealing lighting experience. This luminaire can be surface mounted directly to the ceiling or pendant mounted using rigid conduit. Its light-weight design with quick and easy mounting plate allows simple installation and hands-free wiring. Whether it's new construction, or a retrofit installation, the Garage and Canopy fixture will provide years of trouble free operation and keep you on budget.

## Product data

| General information           |                   | Conduit Connection       |   |
|-------------------------------|-------------------|--------------------------|---|
| Lamp Source Code              | LED               | 7/8 inch knockout        |   |
| Colour Temperature            | 4000 K            | Mechanical and housing   |   |
| CRI                           | 70                | Shape                    | Square  |
| Photometric Distribution Type | Type V            | Material                 | Aluminum                                      |
| Mounting                      | Surface Suspended | Approval and application |   |
| B.U.G. Rating                 | B2U3G1            | Safety Listing           | UL  |
| Grade                         | Value Grade       | Energy Certifications    | DLC Standard cULus                            |
| Operating and electrical      |                   | IP Rating                | IP66 [ Dust penetration-protected, jet-proof] |
| Voltages                      | 120/208/240/277 V | Vibration Rating         | 1.5G  |
| Luminaire Input Watts         | 37 W              |                          |   |

# LED General Purpose Garage & Canopy GC

|  |                      |
|--|----------------------|
| <b>Initial performance (IEC compliant)</b> |                      |
| Luminaire Lumens                           | 4735                 |
| Efficacy                                   | 128 lm/W             |
| <b>Application conditions</b>              |                      |
| Ambient temperature range                  | -40 °C to 40 °C      |
| Max Ambient Temp                           | 40 °C                |
| Min Ambient Temp                           | -40 °C               |
| Min Ambient Temp-DUP(do not use)           | -40 °C               |
| <b>Product data</b>                        |                      |
| Order product name                         | GC40-NW-G1-SM-5-8-BZ |

|                                 |  |
|---------------------------------|--|
| EAN/UPC - Product               | 783352024251   |
| Order code                      | GC40-NW-G1-SM-5-8-BZ                                 |
| Numerator - Quantity Per Pack   | 1  |
| Numerator - Packs per outer box | 1  |
| Material Nr. (12NC)             | 912401468304   |
| Net Weight (Piece)              | 2.000 kg   |
| Catalog Number                  | GC40-NW-G1-SM-5-8-BZ                                 |
| Catalog Number Description      | LED, 40W, 4000K, Type 5 Optics, Textured Dark Bronze |

